



## CT120200LO, Cable Tie, 2" Max Bundle, 120 Lb Tensile, UV Black

By Burndy  
Catalog # [CT120200LO](#)



UV Black Nylon 6/6 Cable Tie, 2" Max. Bundle Dia, 120 Lbs, 8.87" Long, 0.30" Wide.

### Features

Standard Cable Tie

### Application

For Outdoor Applications

### General

Catalog Number	CT120200LO
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Standard
Trade Name	UNIRAP™
Type	Standard
UPC	781810333440

### Dimensions

Dimension - Bundle Diameter Max inch	2
--------------------------------------	---

Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9 in
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

### Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	2500
Minimum Pack Quantity	50

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)  
[Sales Drawings - 50080813](#)  
[Specifications - CT120200LO](#)