



# CT120300LO, Cable Tie, 3" Max Bundle, 120 Lb Tensile, UV Black

By Burndy  
Catalog # [CT120300LO](#)

UV Black Nylon 6/6 Cable Tie, 3" Max. Bundle Dia, 120 Lbs, 11.87" Long, 0.30" Wide.



### Features

Standard Cable Tie

### Application

For Outdoor Applications

### General

Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Standard
Trade Name	UNIRAP™
Type	Standard
UPC	781810333464

### Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

### Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	2000
Minimum Pack Quantity	50
Packaging Type	Bag

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)  
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.