



CT120350SSBC0, Nylon Cable Tie, 120 lb Tensile Strength, Stainless Steel Barb, 13.78" Long, Black

By Burndy
Catalog # [CT120350SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 13.78 IN L, .39 IN W,
Tensile Strength: 120 Lbs, Install with MK9, TWT2.



Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength N	124
Rating - Minimum Tensile Strength lbs	120 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565049

Dimensions

Dimension - Bundle Diameter Max inch	3.82
Dimension - L Length Overall mm	350 mm
Dimension - Length Overall inch	13.78 in
Dimension - Width inch	0.39 in
Dimension - Width mm	10 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2500
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT120350SSBCO-SPEC-EN | REV 5/2024