



# CT120400D00, Cable Tie, 120 Lb Tensile

By Burndy  
Catalog # [CT120400D00](#)



Nylon UNIRAP - 120 Lb. Tensile Strength.

## Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

## General

Catalog Number	CT120400D00
Color	Black
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Trade Name	UNIRAP™
UPC	781810333419

## Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	383 mm
Dimension - Length Overall inch	15.09 in
Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

## Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-3-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	2000
Minimum Pack Quantity	1000
Packaging Type	Bag

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT120400D00](#)