



## CT120400LO, Cable Tie, 4" Max Bundle, 120 Lb Tensile, UV Black

By Burndy  
Catalog # [CT120400LO](#)



UV Black1 Nylon 6/6 Cable Tie, 4" Max. Bundle Dia, 120 Lbs, 15.25" Long, 0.30" Wide.

### Features

Standard Cable Tie

### Application

For Outdoor Applications

### General

Catalog Number	CT120400LO
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Standard
Trade Name	UNIRAP™
Type	Standard
UPC	781810333488

### Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	383 mm
Dimension - Length Overall inch	15.09 in
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

### Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Military Spec Number	MS3367-3-0
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	2000
Minimum Pack Quantity	50

### Product Assets

- [3D Models - CT120400LO\\_MODEL-IGES](#)
- [3D Models - CT120400LO\\_MODEL-PDF](#)
- [3D Models - CT120400LO\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT120400LO](#)