



CT120400LUG, Cable Tie, 120 Lb Tensile, Natural, Universal Grade

By Burndy
Catalog # [CT120400LUG](#)



Nylon UNIRAP - 120 Lb. Tensile Strength.

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

General

Catalog Number	CT120400LUG
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	120
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810469170

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	370 mm
Dimension - Length Overall inch	14.57 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6000
Minimum Pack Quantity	50

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT120400LUG](#)