



## CT120400SSBC0, Nylon Cable Tie, 120 lb Tensile Strength, Stainless Steel Barb, 15.75" Long, Black

By Burndy

Catalog # [CT120400SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 15.75 IN L, .39 IN W,  
Tensile Strength: 120 Lbs, Install with MK9, TWT2.



### Features

Stainless Steel Barb Tie

### Application

For use with self-locking stainless steel barb

### General

Catalog Number	CT120400SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength N	124
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565063

### Dimensions

Dimension - Bundle Diameter Max inch	4.33
Dimension - L Length Overall mm	400 mm

Dimension - Length Overall inch	15.75 in
Dimension - Width mm	0 mm

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT120400SSBC0](#)