



CT120500SSBC0, Nylon Cable Tie, 120 lb Tensile Strength, Stainless Steel Barb, 17.72" Long, Black

By Burndy
Catalog # [CT120500SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 17.72 IN L, .39 IN W,
Tensile Strength: 120 Lbs, Install with MK9, TWT2.



Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT120500SSBC0
Color	Black
EU RoHS Indicator	Contact Manufacturer
Material	NYLON 6/6
Rating - Minimum Tensile Strength N	124
Rating - Minimum Tensile Strength lbs	120 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565087

Dimensions

Dimension - Bundle Diameter Max inch	4.92
Dimension - L Length Overall mm	450 mm
Dimension - Length Overall inch	17.72 in
Dimension - Width inch	0.39 in
Dimension - Width mm	10 mm

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2000
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30022708](#)
[Specifications - CT120500SSBC0](#)