



# CT120800L, Cable Tie, 120 Lb Tensile, Natural

By Burndy  
Catalog # [CT120800L](#)

Nylon cable Tie, 120 lbs, Install with TWT2, MK9, CTT50.



## Features

Standard Cable Tie

## Application

For general purpose applications

## General

Catalog Number	CT120800L
Color	Natural
Color Code	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength N	120
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP
Tool Type	Standard
Trade Name	UNIRAP
Type	CT-L
UPC	781810661079
UPC 12 Digit	7818106610799

## Dimensions

Dimension - Bundle Diameter Max inch	8
Dimension - L Length Overall mm	742 mm
Dimension - Length Overall inch	29.2 in
Dimension - Thread Size	-
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	50

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT120800L](#)