



# CT120800L00, Cable Tie, 120 Lb Tensile, Black

By Burndy  
Catalog # [CT120800L00](#)



Nylon cable Tie, 120 lbs.

## Features

Standard Cable Tie

## Application

For connecting cable to ground rod

## General

Color	UV Black (Mil. Spec.)
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP
Tool Type	Standard
Trade Name	UNIRAP™
Type	STANDARD
UPC	781810661086

## Dimensions

Dimension - Bundle Diameter Max inch	8
Dimension - L Length Overall mm	724 mm
Dimension - Length Overall inch	28.51 in
Dimension - Width inch	0.30 in
Dimension - Width mm	7.6 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	50

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CT120800L00-SPEC-EN | REV 5/2024