



CT1751100Q0, Cable Tie, 11" Max Bundle, 175 Lb Tensile, UV Black

By Burndy
Catalog # [CT1751100Q0](#)

UV Black Nylon 6/6 Cable Tie, 11" Max. Bundle Dia, 175 Lbs, 36" Long, 0.35" Wide.



Features

- Standard Cable Tie

Application

For Outdoor Applications

General

Color	UV Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334133

Dimensions

Dimension - Bundle Diameter Max inch	11
Dimension - L Length Overall mm	927 mm
Dimension - Length Overall inch	36.50 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Military Spec Number	MS3367-13-0
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT1751100Q0-SPEC-EN | REV 1/2024