



## CT1751400Q0, Cable Tie, 15" Max Bundle, 175 Lb Tensile, UV Black

By Burndy  
Catalog # [CT1751400Q0](#)



Nylon cable ties, Tensile strength-175 Lbs, Color- UV Black, 48.00"L, 0.35"W, 15.00" Bundle Dia.

### Features

Standard Cable Tie

### General

Catalog Number	CT1751400Q0
Color	UV Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810334140

### Dimensions

Dimension - Bundle Diameter Max inch	15
Dimension - L Length Overall mm	1219 mm
Dimension - Length Overall inch	48.00 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Packaging Type	Bag

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)  
[Sales Drawings - 50080813](#)  
[Specifications - CT1751400Q0](#)