



CT175500Q0, Cable Tie, 175 Lb Tensile, Black

By Burndy
Catalog # [CT175500Q0](#)



UNIRAP, CT-Q, Standard Cable Ties, Install with TWT2, MK9, CTT50, For general purpose applications, RoHS Under Investigation
Material: Nylon 6/6 UV.

Features

Standard Cable Tie

Application

For general purpose applications

General

Color	UV Black
EU RoHS Indicator	Contact Manufacturer
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	32 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Cable Ties
UPC	781810661116

Dimensions

Dimension - Bundle Diameter Max inch	5.5
Dimension - L Length Overall mm	460 mm
Dimension - Length Overall inch	18.10 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1000
Minimum Pack Quantity	25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.