

# CT175600Q, Cable Tie, 6" Max Bundle, 175 Lb Tensile, Natural

By Burndy  
Catalog # [CT175600Q](#)



Natural Nylon 6/6 Cable Tie, 6" Max. Bundle Dia, 175 Lbs, 21" Long, 0.35" Wide.

## Features

Standard Cable Tie

## Application

For General Purpose

## General

|                                       |                  |
|---------------------------------------|------------------|
| Catalog Number                        | CT175600Q        |
| Color                                 | Natural          |
| EU RoHS Indicator                     | Yes              |
| Material                              | NYLON 6/6        |
| Military Specification                | MS3367           |
| Operating Temperature Celcius Max     | 85 °C            |
| Operating Temperature Celcius Min     | 0 °C             |
| Rating - Minimum Tensile Strength lbs | 175              |
| Sub Brand                             | UNIRAP,CABLE TIE |
| Tool Type                             | Heavy            |
| Trade Name                            | UNIRAP™          |
| Type                                  | Heavy            |
| UPC                                   | 781810333631     |

## Dimensions

|                                      |          |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 7        |
| Dimension - L Length Overall mm      | 622 mm   |
| Dimension - Length Overall inch      | 24.51 in |

|                        |         |
|------------------------|---------|
| Dimension - Width inch | 0.35 in |
| Dimension - Width mm   | 8.9 mm  |

## Certifications And Compliance

|                                    |                               |
|------------------------------------|-------------------------------|
| Buy American Compliant             | Yes                           |
| Certification - 94V0 Rated         | N                             |
| Certification - CSA Approved       | No                            |
| Certification - ETL                | No                            |
| Certification - UL Recognized      | Yes                           |
| Certification - UV Rated           | No                            |
| Certification - cULus              | No                            |
| Industry Standard(s)               | Military Specified (Mil-Spec) |
| Military Spec Number               | MS3367-10-9                   |
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM                            |
| UL Listed                          | No                            |

## Logistics

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 500 |
| Minimum Pack Quantity | 25  |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT175600Q](#)