



CT175600Q0, Cable Tie, 175 Lb Tensile, UV Black

By Burndy
Catalog # [CT175600Q0](#)



Nylon 6/6 Standard Cable Tie, UV Black, 175 Lbs Min Ten Strgth, 21.00" L, 0.35" W.

Features

Standard Cable Tie

Application

For Outdoor Applications

General

Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334119

Dimensions

Dimension - Bundle Diameter Max inch	7
Dimension - L Length Overall mm	622 mm
Dimension - Length Overall inch	24.51 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-10-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT175600Q0-SPEC-EN | REV 5/2024