



CT175600Q0UG, Cable Tie, 6" Max Bundle, 175 Lb Tensile, UV Black, Universal Grade

By Burndy
Catalog # [CT175600Q0UG](#)



Universal grade cable Ties, Nylon 6/6 UV Stabilized, 175 Lbs, 21" L, UV Black, 6" Bundle Dia, Package: 25.

Features

Standard Cable Tie

Application

For both field and production line use

General

Catalog Number	CT175600Q0UG
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	175
Sub Brand	CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	CT_UG
UPC	781810499160

Dimensions

Dimension - Bundle Diameter Max inch	6
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1500
Minimum Pack Quantity	25

Product Assets

- [3D Models - CT175600Q0UG_MODEL-STEP](#)
- [3D Models - CT175600Q0UG_MODEL-IGES](#)
- [3D Models - CT175600Q0UG_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 30002600](#)
- [Specifications - CT175600Q0UG](#)