



CT175600QUG, Cable Tie, 6" Max Bundle, 175 Lb Tensile, Natural, Universal Grade



By Burndy
Catalog # [CT175600QUG](#)

Nylon cable ties, Tensile strength-175 Lbs, Color- Natural,24"L, 0.35"W, 6.00" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT175600QUG
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810499153

Dimensions

Dimension - Bundle Diameter Max inch	6
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1500
Minimum Pack Quantity	25

Product Assets

- [3D Models - CT175600QUG_MODEL-IGES](#)
- [3D Models - CT175600QUG_MODEL-STEP](#)
- [3D Models - CT175600QUG_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 30002600](#)
- [Specifications - CT175600QUG](#)