



CT175800Q0, Cable Tie, 8" Max Bundle, 175 Lb Tensile, Black

By Burndy
Catalog # [CT175800Q0](#)



Nylon cable tie, Tensile strength: 175lb, Bundle dia: 8.

Features

Standard Cable Tie

Application

For connecting cable to ground rod

General

Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP
Tool Type	Heavy
Trade Name	UNIRAP™
Type	STANDARD
UPC	781810661123

Dimensions

Dimension - Bundle Diameter Max inch	8.9
Dimension - L Length Overall mm	830 mm
Dimension - Length Overall inch	32.67 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.