



# CT175900Q00, Cable Tie, 8.75" Max Bundle, 175 Lb Tensile, UV Black

By Burndy  
Catalog # CT175900Q00



Nylon cable ties, Tensile strength-175 Lbs, Color- UV Black, 36.50"L, 0.34"W, 8.75" Bundle Dia.

## Features

Standard Cable Tie

## General

Catalog Number	CT175900Q00
Color	UV Black (Mil. Spec.)
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810334096

## Dimensions

Dimension - Bundle Diameter Max inch	8.75 in
Dimension - L Length Overall mm	927 mm
Dimension - Length Overall inch	36.50 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

## Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-13-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	25
Packaging Type	Bag

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT175900Q00](#)