



CT18075C0, Cable Tie, .75" Max Bundle, 18 Lb Tensile, UV Black

By Burndy
Catalog # [CT18075C0](#)



UV Black Nylon 6/6 Cable Tie, 0.75" Max Bundle Dia, 18 Lbs, 0.10" Wide.

Features

Standard Cable Tie

Application

For Outdoor Applications

General

Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	18
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Mini
Trade Name	UNIRAP™
Type	Mini
UPC	781810331743

Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.10 in
Dimension - Width inch	0.10 in
Dimension - Width mm	2.5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-4-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	100

Product Assets

[3D Models - CT18075C0_MODEL-PDF](#)
[3D Models - CT18075C0_MODEL-IGES](#)
[3D Models - CT18075C0_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CT18075C0-SPEC-EN | REV 5/2024