



CT18075C00, Cable Tie, .75" Max Bundle, 18 Lb Tensile, UV Black

By Burndy
Catalog # [CT18075C00](#)



Nylon cable ties, Tensile strength-18 Lbs, Color- UV Black, 04.10"L, 0.10"W, 0.75" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT18075C00
Color	UV Black (Mil. Spec.)
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	18
Tool Type	Mini
Trade Name	UNIRAP™
UPC	781810331682

Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.10 in
Dimension - Width inch	0.10 in
Dimension - Width mm	2.5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-4-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT18075C00](#)