



CT18075CUG, Cable Tie, .75" Max Bundle, 18 Lb Tensile, Natural, Universal Grade



By Burndy
Catalog # [CT18075CUG](#)

Nylon cable ties, Tensile strength-18 Lbs, Color- Natural, 03.94"L, 0.10"W, 0.75" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT18075CUG
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	18
Tool Type	Mini
Trade Name	UNIRAP™
UPC	781810468920

Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - L Length Overall mm	101 mm
Dimension - Length Overall inch	3.94 in
Dimension - Width inch	0.10 in
Dimension - Width mm	2.5 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	35000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT18075CUG](#)