



# CT18075M0UG, Cable Tie, .75" Max Bundle, 18 Lb Tensile, UV Black, Universal Grade



By Burndy  
Catalog # [CT18075M0UG](#)

Nylon cable ties, Tensile strength-18 Lbs, Color- UV Black, 04.00"L, 0.10"W, 0.75" Bundle Dia.

## Features

Standard Cable Tie

## General

Catalog Number	CT18075M0UG
Color	Black
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	18 lb
Trade Name	UNIRAP™
UPC	781810499085

## Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Width inch	0.1 in
Dimension - Width mm	2.5 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	35000
Minimum Pack Quantity	1000

## Product Assets

- [3D Models - CT18075M0UG\\_MODEL-IGES](#)
- [3D Models - CT18075M0UG\\_MODEL-PDF](#)
- [3D Models - CT18075M0UG\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 30002579](#)
- [Specifications - CT18075M0UG](#)