



## CT18100SSBM0, Nylon Cable Tie, 18 lb Tensile Strength, Stainless Steel Barb, 4.02" Long, Black

By Burndy

Catalog # [CT18100SSBM0](#)

Nylon Stainless Steel BARB Cable Ties, 4.02 IN L, .09 IN W, Tensile Strength: 18 Lbs.



### Features

Stainless Steel Barb Tie

### Application

For use with self-locking stainless steel barb

### General

Catalog Number	CT18100SSBM0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	18 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565100

### Dimensions

Dimension - Bundle Diameter Max inch	0.91
Dimension - L Length Overall mm	102 mm

Dimension - Length Overall inch	4.02 in
Dimension - Width inch	0.09 in
Dimension - Width mm	2 mm

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	3000
Minimum Pack Quantity	1000

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT18100SSBM0](#)