



CT18200M, Cable Tie, 2" Max Bundle, 18 Lb Tensile, Natural

By Burndy
Catalog # [CT18200M](#)



Natural Nylon 6/6 Cable Tie, 2" Max. Bundle Dia, 18 Lbs, 8" Long,.

Features

Standard Cable Tie

Application

For General Purpose

General

Catalog Number	CT18200M
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	18
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Mini
UPC	781810331675

Dimensions

Dimension - Bundle Diameter Max inch	2.10 in
Dimension - L Length Overall mm	208 mm
Dimension - Length Overall inch	8.18 in

Dimension - Width inch	0.09 in
Dimension - Width mm	2 mm

Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	10000
Minimum Pack Quantity	1000

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT18200M](#)