



## CT18200SSBC0, Nylon Cable Tie, 18 lb Tensile Strength, Stainless Steel Barb, 7.91" Long, Black

By Burndy

Catalog # [CT18200SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 7.91 IN L, .09 IN W, Tensile Strength: 18 Lbs,Max bundle dia:2.01".

### Features

Stainless Steel Barb Tie

### Application

For use with self-locking stainless steel barb

### General

Catalog Number	CT18200SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	18
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564462

### Dimensions

Dimension - Bundle Diameter Max inch	2.01
Dimension - L Length Overall mm	201 mm



Dimension - Length Overall inch 7.91 in

Dimension - Width inch 0.09 in

Dimension - Width mm 2 mm

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	EX

### Logistics

Carton Quantity	3000
Minimum Pack Quantity	100

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30022708](#)  
[Specifications - CT18200SSBC0](#)