



# CT18200SSBM, Nylon Cable Tie, 18 lb Tensile Strength, Stainless Steel Barb, 7.91" Long, Natural

By Burndy  
Catalog # [CT18200SSBM](#)

Nylon Stainless Steel BARB Cable Ties, 7.91 IN L, .09 IN W, Tensile Strength: 18 Lbs.



## Features

Stainless Steel Barb Tie

## Application

For use with self-locking stainless steel barb

## General

Catalog Number	CT18200SSBM
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	18 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565117

## Dimensions

Dimension - Bundle Diameter Max inch	2.01
Dimension - L Length Overall mm	201 mm

Dimension - Length Overall inch	7.91 in
Dimension - Width inch	0.09 in
Dimension - Width mm	2 mm

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	3000
Minimum Pack Quantity	1000

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT18200SSBM](#)