



CT2501000RQ, Cable Tie, 10" Max Bundle, 250 Lb Tensile, Natural, Releasable

By Burndy

Catalog # [CT2501000RQ](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 34.00"L, 0.50"W, 10.00" Bundle Dia.

Features

Releaseable

General

| | |
|---------------------------------------|--------------|
| Catalog Number | CT2501000RQ |
| Color | Natural |
| Material | NYLON 6/6 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 250 |
| Trade Name | UNIRAP™ |
| UPC | 781810334881 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 10 |
| Dimension - L Length Overall mm | 864 mm |
| Dimension - Length Overall inch | 34.00 in |

| | |
|------------------------|---------|
| Dimension - Width inch | 0.50 in |
| Dimension - Width mm | 13 mm |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - 94V0 Rated | N |
| Certification - CSA Approved | No |
| Certification - UV Rated | No |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 1000 |
| Minimum Pack Quantity | 1000 |
| Packaging Type | Bag |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_G_P13Releasable](#)
- [Sales Drawings - 50034347](#)
- [Specifications - CT2501000RQ](#)