



CT250200RQ0, Cable Tie, 2.25" Max Bundle, 250 Lb Tensile, UV Black, Releasable

By Burndy
Catalog # [CT250200RQ0](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- UV Black,
09.00"L, 0.50"W, 02.25" Bundle Dia.

Features

Releaseable

General

Catalog Number	CT250200RQ0
Color	Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810334812

Dimensions

Dimension - Bundle Diameter Max inch	2.25
Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9 in

Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1500
Minimum Pack Quantity	1500
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_REL_CABLETIE_LineArt](#)
- [Sales Drawings - 50034347](#)
- [Specifications - CT250200RQ0](#)