



## CT250500RQ, Cable Tie, 6" Max Bundle, 250 Lb Tensile, Natural, Releasable

By Burndy

Catalog # [CT250500RQ](#)

Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 23.00"L, 0.50"W, 06.00" Bundle Dia.



### Features

Releaseable

### General

Catalog Number	CT250500RQ
Color	Natural
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Trade Name	UNIRAP™
UPC	781810334829

### Dimensions

Dimension - Bundle Diameter Max inch	6
Dimension - L Length Overall mm	589 mm
Dimension - Length Overall inch	23 in

Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

### Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	700
Minimum Pack Quantity	25
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_REL\\_CABLETIE\\_LineArt](#)
- [Sales Drawings - 50034347](#)
- [Specifications - CT250500RQ](#)