



# CT250500RQ0, Cable Tie, 250 Lb Tensile, UV Black, Releasable

By Burndy  
Catalog # [CT250500RQ0](#)



Nylon 6/6 Standard Releasable Cable Tie, UV Black, 250 Lbs  
Min Ten Strgth, 20.00" L, 0.50" W.

## Features

Releaseable

## Application

For Use Where Service Requires Adding Or Subtracting Wires From An Existing Wire Bundle

## General

Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Heavy Duty Releasable
UPC	781810334836

## Dimensions

Dimension - Bundle Diameter Max inch	6
Dimension - L Length Overall mm	559 mm
Dimension - Length Overall inch	22 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

## Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	25

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_REL\\_CABLETIE\\_LineArt](#)  
[Sales Drawings - 50034347](#)



A proud member of the Hubbell Family.