



## CT250600Q, Cable Tie, 6.1" Max Bundle, 250 Lb Tensile, Natural

By Burndy  
Catalog # [CT250600Q](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 22.80"L, 0.50"W, 06.10" Bundle Dia.

### Features

Standard Cable Tie

### General

Catalog Number	CT250600Q
Color	Natural
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Tool Type	Heavy
UPC	781810334164

### Dimensions

Dimension - Bundle Diameter Max inch	6.10 in
Dimension - L Length Overall mm	579 mm
Dimension - Length Overall inch	22.80 in
Dimension - Width inch	0.50 in

Dimension - Width mm 13 mm

### Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Packaging Type	Bag

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)  
[Sales Drawings - 50080813](#)  
[Specifications - CT250600Q](#)