



CT250600Q0, Cable Tie, 6" Max Bundle, 250 Lb Tensile, UV Black

By Burndy
Catalog # [CT250600Q0](#)



UV Black Nylon 6/6 Cable Tie, 6" Max. Bundle Dia, 250 Lbs, 23" Long, 0.50" Wide.

Features

Standard Cable Tie

Application

For Outdoor Applications

General

Catalog Number	CT250600Q0
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334645

Dimensions

Dimension - Bundle Diameter Max inch	6.10 in
Dimension - L Length Overall mm	579 mm
Dimension - Length Overall inch	22.80 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	25

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT250600Q0](#)