



CT250800Q, Cable Tie, 8.43" Max Bundle, 250 Lb Tensile, Natural

By Burndy
Catalog # [CT250800Q](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 28.70"L, 0.50"W, 08.43" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT250800Q
Color	Natural
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Tool Type	Heavy
UPC	781810334287

Dimensions

Dimension - Bundle Diameter Max inch	8.43 in
Dimension - L Length Overall mm	729 mm
Dimension - Length Overall inch	28.70 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT250800Q](#)