



## CT250800Q0, Cable Tie, 8.43" Max Bundle, 250 Lb Tensile, UV Black

By Burndy  
Catalog # [CT250800Q0](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- UV Black, 28.70"L, 0.50"W, 08.43" Bundle Dia.

### Features

Standard Cable Tie

### General

Catalog Number	CT250800Q0
Color	UV Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810334652

### Dimensions

Dimension - Bundle Diameter Max inch	8.43 in
Dimension - L Length Overall mm	729 mm
Dimension - Length Overall inch	28.70 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

### Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	500
Minimum Pack Quantity	25
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT250800Q0](#)