



CT250800Q0UG, Cable Tie, 8" Max Bundle, 250 Lb Tensile, UV Black, Universal Grade

By Burndy
Catalog # [CT250800Q0UG](#)

Nylon cable ties, Tensile strength-250 Lbs, Color- UV Black, 29.00"L, 0.50"W, 08.00" Bundle Dia.

Features

- Releasable Cable Tie
- Specially suitable for prototype construction or temporary installation
- Also suitable where service often requires adding or subtracting wires from an existing bundle

General

Catalog Number	CT250800Q0UG
Color	UV Black
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	250
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810643426

Dimensions

Dimension - Bundle Diameter Max inch	8
Dimension - L Length Overall mm	737 mm
Dimension - Length Overall inch	29.00 in

Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50020964](#)
- [Specifications - CT250800Q0UG](#)