

CT30125C, Cable Tie, 1.25" Max Bundle, 30 Lb Tensile, Natural

By Burndy
Catalog # [CT30125C](#)



Natural Nylon 6/6 Cable Tie, 1.25" Max. Bundle Dia, 30 Lbs, 6" Long.

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Application

For General Purpose

General

Catalog Number	CT30125C
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Intermediate
Type	Intermediate
UPC	781810331804

Dimensions

Dimension - Bundle Diameter Max inch	1.40 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.84 in
Dimension - Width inch	0.14 in

Dimension - Width mm 4 mm

Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-9
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	100

Product Assets

- [3D Models - CT30125C_MODEL-IGES](#)
- [3D Models - CT30125C_MODEL-PDF](#)
- [3D Models - CT30125C_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT30125C](#)