



CT30125COUG, Cable Tie, 1.25" Max Bundle, 30 Lb Tensile, UV Black, Universal Grade

By Burndy
Catalog # [CT30125COUG](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- UV Black, 05.90"L, 0.13"W, 01.25" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT30125COUG
Color	UV Black
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	30
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810469040

Dimensions

Dimension - Bundle Diameter Max inch	1.25 in
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.90 in
Dimension - Width inch	0.13 in
Dimension - Width mm	3 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	40000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT30125COUG](#)