



# CT30125CUG, Cable Tie, 1.25" Max Bundle, 30 Lb Tensile, Natural, Universal Grade



By Burndy  
Catalog # [CT30125CUG](#)

Nylon cable ties, Tensile strength-250 Lbs, Color- Natural, 05.90"L, 0.13"W, 01.25" Bundle Dia.

## Features

Standard Cable Tie

## General

Catalog Number	CT30125CUG
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	30
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810469057

## Dimensions

Dimension - Bundle Diameter Max inch	1.25
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.90 in
Dimension - Width inch	0.13 in
Dimension - Width mm	3.3 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	40000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 10092186](#)
- [Specifications - CT30125CUG](#)