



## CT30125M0, Cable Tie, 1.25" Max Bundle, 30 Lb Tensile, UV Black

By Burndy  
Catalog # [CT30125M0](#)



Nylon cable ties, Tensile strength-250 Lbs, Color- UV Black, 05.75"L, 0.13"W, 01.25" Bundle Dia.

### Features

Standard Cable Tie

### General

Catalog Number	CT30125M0
Color	Black
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Trade Name	UNIRAP™
UPC	781810332313

### Dimensions

Dimension - Bundle Diameter Max inch	1.25
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.75 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3.6 mm

### Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000
Packaging Type	Bag

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)  
[Sales Drawings - 50080813](#)  
[Specifications - CT30125M0](#)