



CT30125M00, Cable Tie, 1.4" Max Bundle, 30 Lb Tensile, UV Black

By Burndy
Catalog # [CT30125M00](#)



Nylon cable ties, Tensile strength-30 Lbs, Color- UV Black, 05.84"L, 0.14"W, 01.40" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT30125M00
Color	Black
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Trade Name	UNIRAP™
UPC	781810332290

Dimensions

Dimension - Bundle Diameter Max inch	1.40 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.84 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT30125M00](#)