



CT40137SSBC0, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 5.91" Long, Black

By Burndy
Catalog # [CT40137SSBC0](#)



Nylon Stainless Steel BARB Cable Ties, 5.91 IN L, .14 IN W, Tensile Strength: 40 Lbs,Max bundle dia:1.38".

Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT40137SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564523

Dimensions

Dimension - Bundle Diameter Max inch	1.38
Dimension - L Length Overall mm	150 mm

Dimension - Length Overall inch	5.91 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	3000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT40137SSBC0](#)