




CT40200CUG, Cable Tie, 2" Max Bundle, 40 Lb Tensile, Natural, Universal Grade

By Burndy
Catalog # [CT40200CUG](#)



Nylon cable ties, Tensile strength-40 Lbs, Color- Natural, 07.90"L, 0.15"W, 02.00" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT40200CUG
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810469064

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	201 mm
Dimension - Length Overall inch	7.90 in
Dimension - Width inch	0.15 in
Dimension - Width mm	3.8 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	13000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50127260](#)
- [Specifications - CT40200CUG](#)