



## CT40200M, Cable Tie, 2.37" Max Bundle, 40 Lb Tensile, Natural

By Burndy  
Catalog # [CT40200M](#)



Nylon cable ties, Tensile strength-40 Lbs, Color- Natural, 08.87"L, 0.14"W, 02.37" Bundle Dia.

### Features

Standard Cable Tie

### General

Catalog Number	CT40200M
Color	Natural
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	40
Trade Name	UNIRAP™
UPC	781810332030

### Dimensions

Dimension - Bundle Diameter Max inch	2.37 in
Dimension - L Length Overall mm	225 mm
Dimension - Length Overall inch	8.87 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

### Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT40200M](#)