



## CT40200SSBC0, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 7.87" Long, Black

By Burndy

Catalog # [CT40200SSBC0](#)



Nylon Stainless Steel BARB Cable Ties, 7.87 IN L, .15 IN W,  
Tensile Strength: 40 Lbs,Color:Black.

### Features

Stainless Steel Barb Tie

### Application

For use with self-locking stainless steel barb

### General

Catalog Number	CT40200SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564592

### Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm

Dimension - Length Overall inch	7.87 in
Dimension - Width inch	0.15 in
Dimension - Width mm	4 mm

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	3000
Minimum Pack Quantity	100

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT40200SSBC0](#)



A Hubbell brand