

# CT40300C, Cable Tie, 3" Max Bundle, 40 Lb Tensile, Natural

By Burndy  
Catalog # [CT40300C](#)



Natural Nylon 6/6 Cable Tie, 3" Max. Bundle Dia, 40 Lbs, 11.50" Long, 0.15" Wide.

## Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

## Application

For General Purpose

## General

Catalog Number	CT40300C
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Intermediate
Trade Name	UNIRAP™
Type	Intermediate
UPC	781810332047

## Dimensions

Dimension - Bundle Diameter Max inch	3.37 in
Dimension - L Length Overall mm	278 mm

Dimension - Length Overall inch	10.96 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

## Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT40300C](#)