



CT40400M00, Cable Tie, 4" Max Bundle, 40 Lb Tensile, UV Black

By Burndy
Catalog # [CT40400M00](#)



Nylon cable ties, Tensile strength-40 Lbs, Color- UV Black, 14.25"L, 0.14"W, 04" Bundle Dia.

Features

Standard Cable Tie

General

Catalog Number	CT40400M00
Color	Black
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	40
Trade Name	UNIRAP™
UPC	781810332375

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	362 mm
Dimension - Length Overall inch	14.25 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

Certifications And Compliance

Certification - 94V0 Rated	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT40400M00](#)