



# CT40400SSBC, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 14.49" Long, Natural

By Burndy  
Catalog # [CT40400SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 14.49 IN L, .14 IN W, Tensile Strength: 40 Lbs,Material:Nylon 6/6.

## Features

Stainless Steel Barb Tie

## Application

For use with self-locking stainless steel barb

## General

Catalog Number	CT40400SSBC
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564561

## Dimensions

Dimension - Bundle Diameter Max inch	4.09
Dimension - L Length Overall mm	368 mm



Dimension - Length Overall inch	14.49 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3 mm

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	8000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT40400SSBC](#)