



CT40400SSBC0, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 14.49" Long, Black

By Burndy
Catalog # [CT40400SSBC0](#)



Nylon Stainless Steel BARB Cable Ties, 14.49 IN L, .14 IN W,
Tensile Strength: 40 Lbs,Color:Black.

Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT40400SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT-SSB
UPC	781810564578

Dimensions

Dimension - Bundle Diameter Max inch	4.09
Dimension - L Length Overall mm	368 mm

Dimension - Length Overall inch	14.49 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	8000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT40400SSBC0](#)