



## CT50175C00, Cable Tie, 1.75" Max Bundle, 50 Lb Tensile, UV Black

By Burndy  
Catalog # [CT50175C00](#)



Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 07.56"L, 0.18"W, 01.87" Bundle Dia.

### Features

Standard Cable Tie

### General

|                                       |                       |
|---------------------------------------|-----------------------|
| Catalog Number                        | CT50175C00            |
| Color                                 | UV Black (Mil. Spec.) |
| Material                              | NYLON 6/6             |
| Military Specification                | MS3367                |
| Operating Temperature Celcius Max     | 85 °C                 |
| Operating Temperature Celcius Min     | -40 °C                |
| Rating - Minimum Tensile Strength lbs | 50                    |
| Tool Type                             | Standard              |
| Trade Name                            | UNIRAP™               |
| UPC                                   | 781810332801          |

### Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1.87 in |
| Dimension - L Length Overall mm      | 192 mm  |
| Dimension - Length Overall inch      | 7.56 in |
| Dimension - Width inch               | 0.18 in |
| Dimension - Width mm                 | 5 mm    |

### Certifications And Compliance

|                                    |                               |
|------------------------------------|-------------------------------|
| Certification - 94V0 Rated         | N                             |
| Certification - CSA Approved       | No                            |
| Certification - ETL                | No                            |
| Certification - UL Recognized      | No                            |
| Certification - UV Rated           | Yes                           |
| Certification - cULus              | No                            |
| Industry Standard(s)               | Military Specified (Mil-Spec) |
| Military Spec Number               | MS3367-1-0                    |
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance        | CM                            |
| Status                             |                               |
| UL Listed                          | No                            |

### Logistics

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 10000 |
| Minimum Pack Quantity | 100   |
| Packaging Type        | Bag   |

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CT\\_UNIRAP\\_CABLE\\_TIE\\_LineArt](#)
- [Sales Drawings - 50080813](#)
- [Specifications - CT50175C00](#)